

	BMP™ 21 Label Printer	Rhino™ 5000	P-Touch® PT-1600/50	P-Touch Edge™	Cougar™ LS9	Brady ID PAL™	Rhino™ 1000	Rhino™ 3000	P-Touch® PT-1400
Material Types	Nylon Cloth	Flexible Nylon	Standard Laminated	Standard Laminated	Polyester	Nylon Cloth	Flexible Nylon	Flexible Nylon	Standard Laminated
	Polyester	Permanent Polyester	Flexible ID	Flexible ID	Polyolefin	Polyester	Permanent Polyester	Permanent Polyester	Flexible ID
	Indoor/Outdoor Vinyl	Vinyl	Extra Strength Adhesive	Extra Strength Adhesive	Vinyl	Vinyl	Vinyl	Vinyl	Extra Strength Adhesive
	Permasleeve	Heat Shrink Tubes	Tamper-Evident	Tamper-Evident	Vinyl Cloth	Permasleeve	Heat Shrink Tubes	Heat Shrink Tubes	Tamper-Evident
	Self Laminating	Non Adhesive Tag	Non-Laminated	Non-Laminated			Non Adhesive Tag	Non Adhesive Tag	Non-Laminated
			Iron-on Fabric	Iron-on Fabric					Iron-on Fabric
		Acid Free	Acid Free					Acid Free	
Print Speed	12.5 mm / sec	N/A	10 mm / sec	10 mm / sec	N/A	10 mm / sec	N/A	N/A	10 mm / sec
Print Technology	203 dpi	180 dpi	180 dpi	180 dpi	203 dpi	180 dpi	180 dpi	180 dpi	180 dpi
PC Connectable	No	No	Yes	Yes	No	No	No	No	No
Keyboard	ABC	ABC	ABC	ABC	ABC	ABC	ABC	ABC	ABC
Power Supply	6 AA batteries and optional AC Adaptor	6 AA batteries and optional AC Adaptor	6 AA batteries	6 AA batteries	6 AA batteries	6 AA batteries and optional AC Adaptor	6 AA batteries and optional AC Adaptor	6 AA batteries and optional AC Adaptor	6 AA batteries
Warranty	1 year limited warranty	1 year limited warranty	1 year limited warranty	2 year limited warranty	1 year limited warranty	1 year limited warranty	1 year limited warranty	1 year limited warranty	1 year limited warranty
Magnet Accessory	Yes	No	No	No	No	No	No	No	No
Wire/Cable Wrap Label Type	Yes	Yes	Yes	Yes	Yes	Yes	No	Yes	Yes
Fixed Length Label Type	Yes	Yes	Yes	Yes	Yes	No	Yes	Yes	Yes
Patch Panel Label Type	Yes	Yes	Yes	Yes	Yes	No	No	No	Yes
Terminal Block Label Type	Yes	Yes	Yes	Yes	Yes	No	No	No	Yes
Flag Label Type	No	No	Yes	Yes	Yes	No	Yes	Yes	Yes

	BMP™21 Label Printer	Rhino™ 5000	P-Touch® PT-1600/50	P-Touch Edge™	Cougar™ LS9	Brady ID PAL™	Rhino™ 1000	Rhino™ 3000	P-Touch® PT-1400
Vertical Print	No	Yes	Yes	Yes	Yes	No	Yes	Yes	Yes
Barcode	Code 39 and 128	Code 39 and 128	Codabar, Code 128, Code 39, EAN/JAN-13, EAN/JAN-8, Industrial 2 of 5, UCC/EAN-128, UPC-A, UPC-E	Codabar, Code 128, Code 39, EAN/JAN-13, EAN/JAN-8, UCC/EAN-128, UPC-A, UPC-E	Code 39 and 128	No	No	No	Codabar, Code 128, Code 39, EAN/JAN-13, EAN/JAN-8, Industrial 2 of 5, UCC/EAN-128, UPC-A, UPC-E
Symbols Hot Key	Yes	Yes	Yes	Yes		No	Yes	No	Yes
Barcode Hot Key	Yes	Yes	Yes	Yes		No	Yes	Yes	Yes
Tape Widths	1/4", 3/8", 1/2", 3/4"	1/4", 3/8", 1/2", 3/4"	1/4", 3/8", 1/2", 3/4", 1"	1/4", 3/8", 1/2", 3/4", 1"	1/4", 3/8", 1/2", 3/4", 1"	3/8", 1/2", 3/4"	3/8", 1/2"	1/4", 3/8", 1/2"	1/4", 3/8", 1/2", 3/4", 1"
Battery Life Indicator	Yes	Yes	Yes	Yes	Yes	No	No	Yes	Yes
Label Memory	Yes, stores 12 files	Yes, stores 10 files	2,000 characters	2,000 characters	10 files	No	No	Yes, stores up to 25 files	2,000 characters
Display Lines	3 lines 39 characters	2 lines 30 characters	2 lines 30 characters	2 lines 30 characters	4 lines 56 characters	1 line 7 characters	1 line 13 characters	1 line 13 characters	2 lines 30 characters
Display Size	2" x 1"	2.25" x 0.7"	2.3" x 0.875"	2.3" x 0.875"		1.25" x 0.75"	1.9" x 0.6"	2.25" x 0.5"	2.3" x 0.875"
Backlit LCD screen	Yes	Yes	No	Yes	Yes	No	No	Yes	No
Printing Multiple Copies	Yes	Yes	Yes	Yes	Yes	No	Yes	Yes	Yes
Protection	Impact resistant rubber on top, bottom and sides of printer	Impact resistant rubber shoe around the printer	No	Impact resistant rubber on top, bottom and sides of printer	Impact resistant rubber on top, bottom and sides of printer	Optional Rubber bumper on top and bottom only	None	Impact resistant rubber shoe around the printer	No
Dimensions	9.2" x 4.6" x 2.6"	8.3" x 4.5" x 2.8"	9.4" x 4.6" x 3.2"	9.25"x5.28"x3.07"		9" x 4.5" x 2"	6" x 4" x 2"	7.5" x 4.5" x 2"	9.3" x 4.5" x 3.1"
Weight	1.66 lbs	1.96 lbs.	1.3 lbs	1.4 lbs	1.8 lbs	1.2 lbs.	0.6 lb.	0.8 lb.	1.19 lbs
Price Range	\$139	\$92 - \$149	\$100 - \$200	\$100-\$200	\$149	\$99	\$49.99	\$88 - \$110	\$50 - \$100

The above information was taken from product packaging/ websites published on or before July 2009.
 Rhino is a trademark of Dymo Corporation, A Newell Rubbermaid Company.
 P-Touch and P-Touch Edge are trademarks of Brother International Corporation.
 Cougar LS9 is a trademark of Panduit Corporation.

© 2009 Brady Worldwide Inc. ALL RIGHTS RESERVED

6555 West Good Hope Rd.
 Milwaukee WI, 53223
 1-888-272-3946
www.bradyid.com

 **BRADY**
 WHEN PERFORMANCE MATTERS MOST™