

NYLON CLOTH



IDEAL FOR:

- Wire & Cable
- Patch Panels
- Terminal Blocks
- Face Plates

16' Long	.375"	.5"	.75"
Black on White	M21-375-499	M21-500-499	M21-750-499
Terminal Block	M21-375-499-TB	M21-500-499-TB	

POLYESTER



IDEAL FOR:

- Components
- Instruments
- Racks & Bins

21' Long	.375"	.5"	.75"
Black on White	M21-375-423	M21-500-423	M21-750-423
Black on Clear	M21-375-430	M21-500-430	M21-750-430

6555 W. Good Hope Rd.
Milwaukee WI, 53223
1-888-272-3946



INDOOR/OUTDOOR VINYL FILM



PROPERTIES:

- Adheres to irregular, curved or rough surfaces
- Stands up to grease, oil and most industrial chemicals
- 5 year average outdoor durability in temperatures from -40°F to 180°F

IDEAL FOR:

- Pipes
- Round Surfaces
- Tools
- Containers
- Bins
- Components
- Instruments
- Panels

21' Long	.375"	.5"	.75"
Black on White	M21-375-580-WT	M21-500-580-WT	M21-750-580-WT
Black on Yellow	M21-375-580-YL	M21-500-580-YL	M21-750-580-YL
Black on Orange	M21-375-580-OR	M21-500-580-OR	M21-750-580-OR
White on Red	M21-375-580-RD	M21-500-580-RD	M21-750-580-RD
White on Blue	M21-375-580-BL	M21-500-580-BL	M21-750-580-BL
White on Green	M21-375-580-GR	M21-500-580-GR	M21-750-580-GR

www.bradyid.com/bmp21



BMP™ 21 LABEL PRINTER

LABEL SELECTION GUIDE

- Wire Markers
- Cable Markers
- Pipes
- Tools
- Bins
- Containers
- Faceplates
- Electrical Panels
- Patch Panels
- Terminal Blocks
- Instruments
- Racks



www.bradyid.com/bmp21

MATERIAL SELECTION GUIDE

BMP™21 Mobile Printer features multiple materials for a variety of applications. Use the chart below to help determine what material works best for your applications



	Flat, Smooth Surface	Textured, Smooth Surface	Large Curved Surface	Wire & Cable
Self-Laminating Vinyl				
PermaSleeve™				
Nylon Cloth				
Indoor/Outdoor Vinyl				
Polyester				

SELF-LAMINATING VINYL



PROPERTIES:

- Self Extinguishing
- Excellent water & oil resistance
- Excellent abrasion resistance

14' Long	.75"	1"	1.25"	1.5"
Black on White	M21-750-427	M21-1000-427	M21-1250-427	M21-1500-427

PERMASLEEVE™ WIRE MARKER SLEEVES



PROPERTIES:

- Heat-Shrinkable
- Self Extinguishing
- Meets MIL-M-81531; MIL-STD-202F; method 215 and UL 224

7' Long	.125"	.187"	.250"	.375"
Black on White	M21-125-C-342	M21-187-C-342	M21-250-C-342	M21-375-C-342